

MST Sprockets



MST DOUBLE STRAND															
No. of Teeth	40 Pitch			50 Pitch			60 Pitch			80 Pitch		100 Pitch		120 Pitch	
	Part Number	List Price		Part Number	List Price		Part Number	List Price		Part Number	List Price	Part Number	List Price	Part Number	List Price
11															
12															
13															
14															
15	D40H15H	122.70		D50P15H	155.20										
16	D40H16H	123.70		D50P16H	156.60										
17	D40H17H	125.60		D50P17H	162.40										
18	D40P18H	127.30		D50P18H	165.20										
19	D40P19H	129.90		D50P19H	166.60										
20	D40P20H	131.90		D50P20H	180.30										
21	D40P21H	135.40		D50P21H	182.80										
22	D40P22H	146.00		D50P22H	191.50										
23	D40P23H	162.60		D50P23H	200.20										
24	D40P24H	165.70		D50Q24H	202.70										
25	D40P25H	174.10		D50Q25H	205.40										
26	D40P26H	181.10		D50Q26H	207.80										
27				D50Q27H	210.90										
28	D40P28H	195.00		D50Q28H	227.20										
30	D40Q30H	197.30		D50Q30H	243.30									D120S30	1926.50
32	D40Q32H	199.70		D50Q32H	263.00										
35	D40Q35H	202.30		D50Q35H	282.60										
36	D40Q36H	204.40		D50Q36H	292.10										
40	D40Q40H	205.00		D50Q40H	306.60										
42	D40Q42H	206.00		D50Q42H	313.90										
45	D40Q45H	270.80		D50Q45H	351.00										
48	D40Q48H	281.20		D50Q48H	369.50										
52	D40Q52H	290.10		D50Q52	446.20										
54	D40Q54H	301.00		D50Q54	473.60										
60	D40Q60H	329.70		D50Q60	547.90										
68	D40Q68	348.80													
70															
72	D40Q72	397.30		D50Q72	701.20										
76	D40Q76	426.60		D50Q76	736.00										
80															
84	D40Q84	466.70		D50Q84	773.10										
95	D40Q95	546.00		D50R95	954.10										
96	D40Q96	579.40		D50R96	964.30										
102	D40Q102	596.00		D50R102	998.60										
112	D40Q112	901.70		D50R112	1122.30										

For chains and/or tooth sizes not indicated above, please contact your nearest *Martin* facility for a quote.

For more information contact your nearest *Martin* Distributor or any of the Branch locations listed below.

USA
General Offices Sales and Manufacturing
Arlington, TX 76015
 3100 Sprocket Drive • 817-258-3000 (FAX 817-258-3333)
Denver, CO 80239
 10800 East 54th Ave. • 303-371-8466 (FAX 303-371-7116)
Danielsville, PA 18038
 3376 Delps Road • 610-837-1841 (FAX 610-837-7337)
Fl. Worth, TX 76110
 3600 McCarr Street • 817-258-3000 (FAX 817-258-3173)
Manfield, TX 76063
 811 4th Avenue 76063 • 817-473-1520 (FAX 817-473-0465)
Montpelier, OH 43543
 350 Airport Road • 419-485-5515 (FAX 419-485-3565)
Sacramento, CA 95814
 1199 Vine Street • 916-441-7172 (FAX 916-441-4600)
Scottsdale, GA 30079
 3303 Church Street • 404-292-8744 (FAX 404-292-7771)
Mini Manufacturing Centers
Milford, MA 01757
 357 Fortune Boulevard • 508-634-3990 (FAX 508-634-3998)

Charlotte, NC 28208
 3901 South I-85 Service Rd. • 704-394-9111 (FAX 704-394-9122)
Des Plaines, IL 60018
 1505 Birchwood Avenue • 847-298-8844 (FAX 847-298-2967)
Commerce, CA 90040
 1520 N. Commerce Ave. • 816-231-5575 (FAX 816-231-1959)
Bloomington, MN 55438
 10601 Hampshire Ave. S. • 952-829-0623 (FAX 952-944-9385)
Portland, OR 97210
 3030 N.W. Industrial • 503-223-7261 (FAX 503-221-0203)
Tampa, FL 33619
 3201 Queen Palm Drive • 813-623-1705 (FAX 813-626-8953)
Wayne, NJ 07470
 7 High Point Drive • 973-633-6700 (FAX 973-633-7196)

Livonia, MI 48150
 12555 Belden Ct. • 734-367-0238 (FAX 734-367-0547)
Abilene, TX • Clarksville, TX • Dallas, TX • Paragould, AR
Manufacturing Only
Sales and Manufacturing
CANADA
Sprocket & Gear Canada Inc.
 896 Meyerside Drive • Mississauga, Ontario, Canada L5T 1R9
 905-670-1991 (FAX 905-670-2110)
(Conveyor Division)
 Box C3, RR #1 • Ayr, Ontario, Canada NOB 1E0
 519-621-0546 (FAX 519-621-4413)
CHINA: Shanghai • Fuzhou • Chengdu
MEXICO
Sprocket & Gear de Mexico, S.A. de C.V.
 Km. 52.8 Carretera, Naucalpan-Toluca • Parque Industrial,
 Toluca 2000 • Calle 3, Manzana VII, Lote 11
 Toluca Edo. de Mexico, C.P. 50200
 011-52-72-790023 (FAX 011-52-72-790024)

MST Sprockets



MST TRIPLE STRAND										
No. of Teeth	40 Pitch			50 Pitch			60 Pitch		80 Pitch	
	Part Number	List Price		Part Number	List Price		Part Number	List Price	Part Number	List Price
13										
14										
15										
16										
17										
18	E40P18H	149.60		E50P18H	199.90					
19	E40P19H	157.80		E50P19H	211.00					
20	E40P20H	166.10		E50P20H	222.00					
21				E50P21H	233.20					
22										
23	E40P23H	191.10		E50P23H	255.30					
24	E40P24H	199.40		E50Q24H	266.50					
25	E40P25H	207.70		E50Q25H	277.40					
26				E50Q26H	288.60					
27	E40P27H	224.20								
28				E50Q28H	310.70					
30	E40Q30H	249.30		E50Q30H	333.10					
32				E50Q32H	355.20					
35	E40Q35H	290.60		E50Q35H	388.50					
36	E40Q36H	299.10		E50Q36H	389.40					
40				E50Q40H	419.80					
42	E40Q42H	317.40		E50Q42H	435.00					
45										
48	E40Q48H	341.80		E50Q48H	506.10					
52	E40Q52H	362.80		E50Q52	664.80					
54	E40Q54H	376.50								
60	E40Q60H	405.90		E50R60	675.20					
68	E40Q68	447.50		E50R68	709.80					
72	E40Q72	498.70		E50R72	849.10					
76	E40Q76	525.10		E50R76	988.40					
84	E40Q84	580.10		E50R84	1040.70					
95	E40Q95	669.30		E50R95	1204.80					
102	E40Q102	796.80		E50R102	1398.70					

For chains and/or tooth sizes not indicated above, please contact your nearest *Martin* facility for a quote.

- Stock • Alterations: Same Day / Next Day Availability
- Made-to-Order: For more information contact your nearest *Martin* Distributor.

MST DOUBLE SINGLE					
Part Number	Bushing	List Price	Part Number	Bushing	List Price
DS40H19H	H	167.20	DS80Q17H	Q1	367.00
DS40H21H	H	189.60	DS80Q19H	Q1	437.40
DS40P23H	P1	179.60	DS80Q20H	Q1	458.00
DS40P24H	P1	191.50	DS80R21H	R1	385.50
DS50H17H	H	208.60	DS80R23H	R1	401.10
DS50P19H	P1	215.30	DS100R17H	R1	504.40
DS50P21H	P1	230.80	DS100R19H	R1	543.10
DS50P23H	P1	235.50	DS100R21H	R1	571.40
DS50P24H	P1	242.80			
DS60P17H	P1	239.10			
DS60P19H	P1	295.30			
DS60Q21H	Q1	290.80			
DS60Q22H	Q1	295.60			
DS60Q23H	Q1	298.10			
DS60Q24H	Q1	305.10			

MST BUSHINGS			MST HUBS	
Part Number	Bore Range	List Price	Part Number	List Price
H*	3/8 - 1-1/2	8.40	HH1	29.30
P1	1/2 - 1-3/4	14.60	HCH1	29.30
P2	3/4 - 1-3/4	16.00	HP1	46.90
P3	1-1/8 - 1-5/8	25.60	HCP1	46.90
Q1	3/4 - 2-11/16	28.70	HP2	82.10
Q2	1 - 2-5/8	31.40	HQ1	93.80
Q3	1-3/8 - 2-1/2	44.90	HCQ1	93.80
R1	1-1/8 - 3-3/4	70.90	HQ2	140.70
R2	1-3/8 - 3-5/8	79.80	HR1	164.10
S1	1-11/16 - 4-1/4	141.80	HR2	351.70
S2	1-7/8 - 4-3/16	177.20	HS1	281.40
U0	2-3/8 - 5-1/2	310.10	HS2	761.80
U1	2-3/8 - 5-1/2	531.70	HU0	820.50
U2	2-7/8 - 5-1/2	620.20	HU1	1084.60
W1	3-3/8 - 7-7/16	1240.40	HU2	1465.60
W2	3-3/8 - 7-7/16	1417.60	HW1	2251.40

* H bushing does not have external key.

Other Quality Products from a World Leader in the Power Transmission Industry.

- Sprockets • Gears • Sheaves • Couplings
- Synchronous • Screw Conveyors
- Drag Conveyors • Bucket Elevators
- Industrial Hand Tools

Depend on consistent quality products readily available for quick delivery. *Martin* offers you the quickest turnaround, the highest inventory levels and the best application assistance in North America.



Martin
SPLIT TAPER™



MST™

sprockets • bushings • hubs