



Screwdrivers






Chrome Vanadium Steel Blades

Rust and Corrosion Resistant Finish

Highly Resistant to Wear and Fatigue, this High-Tech Material Possesses Overall Superior Tensile Strength and Antifatigue Characteristics.

Bonding Agent Fuses to Blade, Resulting in a High Gloss Protective Finish, Keeping Screwdriver Attractive and in Use for Years.

WARNING: Plastic handles are not intended to act as insulation. Never use screwdrivers as prybars or chisels.


 NARROW TIP, ROUND SHANK	Cabinet and Electrical Screwdrivers					
	Blade Length	Blade Width	Type	Wt. Ea. Lbs.	Part No.	Std. Pkg. Qty.
	4	3/16	Cabinet	.14	SDE4	6
	6	3/16	Electrical	.15	SDE6	6
	8	3/16	Electrical	.16	SDE8	6
 WIDENED TIP, ROUND SHANK	Mechanic's and Heavy Duty Screwdrivers					
	Blade Length	Blade Width	Type	Wt. Ea. Lbs.	Part No.	Std. Pkg. Qty.
	4	1/4	Mechanic's	.20	SDR4	6
	6	3/16	Heavy Duty	.30	SDR6	6
	8	3/8	Heavy Duty	.49	SDR8	6
 PRECISION HEAD, ROUND SHANK	Phillips Screwdrivers					
	Blade Length	Phillips Size	Type	Wt. Ea. Lbs.	Part No.	Std. Pkg. Qty.
	3	No. 1	Phillips	.13	SDP3	6
	4	No. 2	Phillips	.20	SDP4	6
	6	No. 3	Phillips	.30	SDP6	6
 STURDY TIP, SQUARE SHANK	Square-Blade Screwdrivers					
	Blade Length	Blade Width	Type	Wt. Ea. Lbs.	Part No.	Std. Pkg. Qty.
	4	1/4	Square	.21	SDS4	6
	6	3/16	Square	.34	SDS6	6
	8	3/8	Square	.55	SDS8	6
	10	3/8	Square	.62	SDS10	6
	12	3/8	Square	.70	SDS12	6
 TIGHT CLEARANCE, STURDY	Stubby Screwdrivers					
	Blade Length	Width/ Size	Type	Wt. Ea. Lbs.	Part No.	Std. Pkg. Qty.
	1 1/2	1/4	Stubby	.10	SDS1	6
	1 1/2	No. 2	Phillips	.10	SDP1	6
			Stubby			6

Screwdrivers Sets



SDP4K
4 Pc. Phillips Screwdriver Set

SDP1 1½" Phillips No. 2 Stubby
SDP3 3" Phillips No. 1
SDP4 4" Phillips No. 2
SDP6 6" Phillips No. 3
P396 Pouch




SDR4K
4 Pc. Combination Screwdriver Mixed Set

SDR4 4" Mechanic's
SDE4 4" Cabinet
SDP3 3" Phillips No. 1
SDP4 4" Phillips No. 2
P595 Pouch



SDR5K
5 Pc. Combination Screwdriver Mixed Set

SDE4 4" Cabinet
SDR4 4" Mechanic's
SDR6 6" Heavy Duty
SDR8 8" Heavy Duty
SDS1 1½" Stubby
P696 Pouch






Screwdrivers Sets



SDR7K

7 Pc. Combination Screwdriver Mixed Set

- SDE4 4" Cabinet
- SDE6 6" Electrical
- SDP3 3" Phillips No. 1
- SDP4 4" Phillips No. 2
- SDP6 6" Phillips No. 3
- SDR4 4" Mechanic's
- SDR6 6" Heavy Duty
- P496 Pouch



SDS3K

3 Pc. Standard Screwdriver Set

- SDS4 4" Square-Blade
- SDS6 6" Square-Blade
- SDS8 8" Square-Blade
- P296 Pouch