


Double Head Open End Wrenches



American Alloy Steel
Drop Forged

15° Angle

Comfortable Grip

Chrome and
Industrial Black

Wrench Opening	Diameter of Head	Thickness of Head	Length	Wt. Ea. Lbs.	Chrome	Std. Pkg. Qty.	Industrial Black	Std. Pkg. Qty.	Wrench Opening
	A × B	C	D		Part No.		Part No.		
1/4 × 5/16	19/32 × 3/4	5/32	4 1/2	.03	1020	6	BLK-1020	6	1/4 × 5/16
3/16 × 11/32	19/32 × 3/4	5/32	4 1/2	.04	1720	6	BLK1720	6	3/16 × 11/32
5/16 × 3/8	19/32 × 3/4	5/32	4 1/2	.04	1721	6	BLK1721	6	5/16 × 3/8
3/8 × 13/32	19/32 × 3/4	5/32	4 1/2	.04	1021	6	BLK1021	6	3/8 × 13/32
3/8 × 7/16	3/4 × 29/32	13/64	4 7/8	.06	1723	6	BLK1723	6	3/8 × 7/16
3/8 × 1/2	3/4 × 29/32	13/64	4 7/8	.06	1723A	6	BLK1723A	6	3/8 × 1/2
7/16 × 1/2	29/32 × 1 1/8	1/4	5 1/4	.13	1725	6	BLK1725	6	7/16 × 1/2
7/16 × 9/16	29/32 × 1 1/8	1/4	5 1/4	.13	1725A	6	BLK1725A	6	7/16 × 9/16
1/2 × 9/16	1 1/16 × 1 1/8	1/4	6 1/8	.19	1725B	6	BLK1725B	6	1/2 × 9/16
1/2 × 5/8	1 1/4 × 1 1/8	13/32	6 1/2	.32	1726	6	BLK1726	6	1/2 × 5/8
5/16 × 5/8	1 1/8 × 1 1/4	13/64	6 3/4	.20	1727	6	BLK1727	6	5/16 × 5/8
3/8 × 11/16	1 1/16 × 1 1/16	19/64	7 1/2	.27	1027C	6	BLK1027C	6	3/8 × 11/16
19/32 × 1 1/16	1 1/16 × 1 1/16	19/64	7 1/2	.27	1027	6	BLK1027	6	19/32 × 1 1/16
5/8 × 1 1/16	1 3/16 × 1 1/16	19/64	7 1/2	.27	1027B	6	BLK1027B	6	5/8 × 1 1/16
3/4 × 3/4	1 1/16 × 1 1/8	5/16	8 1/2	.41	1728	6	BLK1728	6	3/4 × 3/4
5/8 × 3/4	1 1/16 × 1 1/8	5/16	8 1/2	.41	1729	6	BLK1729	6	5/8 × 3/4
11/16 × 3/4	1 1/16 × 1 1/8	5/16	8 1/2	.41	1029B	6	BLK1029B	6	11/16 × 3/4
1 1/16 × 29/32	1 3/16 × 1 1/8	5/16	8 1/2	.41	1029	6	BLK1029	6	1 1/16 × 29/32
1 1/16 × 13/16	1 3/16 × 1 1/8	5/16	8 1/2	.40	1029C	6	BLK1029C	6	1 1/16 × 13/16
1 1/16 × 7/8	1 3/16 × 1 1/8	5/16	8 1/2	.40	1030	6	BLK-1030	6	1 1/16 × 7/8
3/4 × 13/16	1 1/8 × 1 1/4	11/32	9 1/8	.50	1731	6	BLK1731	6	3/4 × 13/16
3/4 × 7/8	1 1/8 × 1 1/4	11/32	9 1/8	.50	1731A	6	BLK1731A	6	3/4 × 7/8
13/16 × 7/8	1 1/8 × 1 1/4	11/32	9 1/8	.50	1731B	6	BLK1731B	6	13/16 × 7/8
7/8 × 15/16	1 11/16 × 1 15/16	3/8	10 3/8	.75	1033A	6	BLK1033A	6	7/8 × 15/16
7/8 × 1	1 11/16 × 1 15/16	3/8	10 3/8	.72	1733	6	BLK1733	6	7/8 × 1
15/16 × 1	1 1/8 × 2 1/8	7/16	11 1/2	1.05	1033C	6	BLK1033C	6	15/16 × 1
7/8 × 1 1/16	1 1/8 × 2 1/8	7/16	11 1/2	1.03	1034	6	BLK1034	6	7/8 × 1 1/16
15/16 × 1 1/16	1 1/8 × 2 1/8	7/16	11 1/2	1.01	1034A	6	BLK1034A	6	15/16 × 1 1/16
1 × 1 1/8	2 1/8 × 2 1/4	7/16	12 1/2	1.18	1735	6	BLK1735	6	1 × 1 1/8
1 1/16 × 1 1/8	2 1/8 × 2 1/4	7/16	12 1/2	1.16	1036B	6	BLK1036B	6	1 1/16 × 1 1/8
1 1/16 × 1 1/4	2 1/4 × 2 3/8	1/2	13 3/4	1.6	1037	6	BLK1037	6	1 1/16 × 1 1/4
1 1/8 × 1 1/4	2 1/4 × 2 3/8	1/2	13 3/4	1.6	1737	6	BLK1737	6	1 1/8 × 1 1/4
1 1/8 × 13/16	2 1/4 × 2 3/8	1/2	13 3/4	1.6	1037A	6	BLK1037A	6	1 1/8 × 13/16
1 1/4 × 1 1/8	2 3/4 × 2 7/8	9/16	15 1/2	2.1	1039B	6	BLK1039B	6	1 1/4 × 1 1/8
1 1/4 × 1 1/16	2 3/4 × 2 7/8	9/16	15 1/2	2.1	1039	6	BLK1039	1	1 1/4 × 1 1/16
1 1/16 × 1 1/2	2 3/4 × 2 7/8	9/16	15 1/2	2.1	1039A	6	BLK1039A	1	1 1/16 × 1 1/2
1 3/8 × 1 1/16	2 3/4 × 2 7/8	9/16	15 1/2	2.0	1039C	6	BLK1039C	1	1 3/8 × 1 1/16
1 1/4 × 1 1/8	2 3/4 × 2 7/8	9/16	15 1/2	2.0	1040	6	BLK1040	1	1 1/4 × 1 1/8
1 7/16 × 1 3/8	2 3/4 × 3 1/4	5/8	17	3.1	1041	1	BLK1041	1	1 7/16 × 1 3/8
1 1/2 × 1 3/8	2 3/4 × 3 1/2	5/8	17	3.1	1041B	1	BLK1041B	1	1 1/2 × 1 3/8
1 11/16 × 1 1/8	3 3/4 × 4 1/8	7/8	19 1/2	7.2	—	—	BLK44A	1	1 11/16 × 1 1/8
1 13/16 × 2	3 3/4 × 4 1/8	7/8	19 1/2	6.9	—	—	BLK45	1	1 13/16 × 2
2 3/16 × 2 3/8	4 13/16 × 4 7/8	1 1/8	23	11.8	—	—	BLK49	1	2 3/16 × 2 3/8
2 1/4 × 2 7/16	4 13/16 × 4 7/8	1 1/8	23	11.7	—	—	BLK49A	1	2 1/4 × 2 7/16



Double Head Open End Wrench Sets

6 Sets of Popular Sizes Provide a Wide Range of Openings in Chrome or Industrial Black Finish.

Chrome Sets					
OE6K		OE8K		OE11K	
OPENING	PART NO.	OPENING	PART NO.	OPENING	PART NO.
$\frac{3}{8} \times \frac{1}{16}$	1723	$\frac{1}{4} \times \frac{3}{16}$	1020	$\frac{1}{4} \times \frac{3}{16}$	1020
$\frac{1}{2} \times \frac{3}{16}$	1725B	$\frac{3}{8} \times \frac{1}{16}$	1723	$\frac{3}{8} \times \frac{3}{8}$	1721
$\frac{5}{8} \times \frac{1}{16}$	1027B	$\frac{1}{2} \times \frac{3}{16}$	1725B	$\frac{3}{8} \times \frac{7}{16}$	1723
$\frac{3}{4} \times \frac{13}{16}$	1731	$\frac{5}{8} \times \frac{11}{16}$	1027B	$\frac{7}{16} \times \frac{1}{2}$	1725
$\frac{7}{8} \times \frac{13}{16}$	1033A	$\frac{3}{4} \times \frac{13}{16}$	1731	$\frac{1}{2} \times \frac{9}{16}$	1725B
$1 \times 1\frac{1}{8}$	1735	$\frac{7}{8} \times \frac{15}{16}$	1033A	$\frac{9}{16} \times \frac{5}{8}$	1727
Kit Bag	C60B	$1 \times 1\frac{1}{8}$	1735	$\frac{3}{8} \times \frac{11}{16}$	1027B
		$1\frac{1}{16} \times 1\frac{1}{4}$	1037	$\frac{3}{4} \times \frac{13}{16}$	1731
		Kit Bag	C81	$\frac{7}{8} \times \frac{15}{16}$	1033A
				$1 \times 1\frac{1}{8}$	1735
				$1\frac{1}{16} \times 1\frac{1}{4}$	1037
				Kit Bag	C110
Industrial Black Sets					
BOE6K		BOE8K		BOE11K	
OPENING	PART NO.	OPENING	PART NO.	OPENING	PART NO.
$\frac{3}{8} \times \frac{1}{16}$	BLK1723	$\frac{1}{4} \times \frac{3}{16}$	BLK-1020	$\frac{1}{4} \times \frac{3}{16}$	BLK-1020
$\frac{1}{2} \times \frac{3}{16}$	BLK1725B	$\frac{3}{8} \times \frac{1}{16}$	BLK1723	$\frac{3}{8} \times \frac{3}{8}$	BLK1721
$\frac{5}{8} \times \frac{1}{16}$	BLK1027B	$\frac{1}{2} \times \frac{3}{16}$	BLK1725B	$\frac{3}{8} \times \frac{7}{16}$	BLK1723
$\frac{3}{4} \times \frac{13}{16}$	BLK1731	$\frac{5}{8} \times \frac{11}{16}$	BLK1027B	$\frac{7}{16} \times \frac{1}{2}$	BLK1725
$\frac{7}{8} \times \frac{13}{16}$	BLK1033A	$\frac{3}{4} \times \frac{13}{16}$	BLK1731	$\frac{1}{2} \times \frac{9}{16}$	BLK1725B
$1 \times 1\frac{1}{8}$	BLK1735	$\frac{7}{8} \times \frac{15}{16}$	BLK1033A	$\frac{9}{16} \times \frac{5}{8}$	BLK1727
Kit Bag	C60B	$1 \times 1\frac{1}{8}$	BLK1735	$\frac{3}{8} \times \frac{11}{16}$	BLK1027B
		$1\frac{1}{16} \times 1\frac{1}{4}$	BLK1037	$\frac{3}{4} \times \frac{13}{16}$	BLK1731
		Kit Bag	C81	$\frac{7}{8} \times \frac{15}{16}$	BLK1033A
				$1 \times 1\frac{1}{8}$	BLK1735
				$1\frac{1}{16} \times 1\frac{1}{4}$	BLK1037
				Kit Bag	C110