


American Alloy Steel

Chrome or Black Finish

12 Point Opening

Drop Forged



Wrench Opening	Diameter of Head	Thickness of Head	Width of Slot	Length	Wt. Ea. Lbs.	Chrome	Industrial Black	Std. Pkg. Qty.	Wrench Opening
	A	B	C	D		Part No.	Part No.		
$\frac{3}{8}$	$\frac{25}{32}$	$\frac{5}{16}$	$\frac{9}{32}$	$6\frac{1}{32}$.18	4112	BLK4112	6	$\frac{3}{8}$
$\frac{7}{16}$	$\frac{27}{32}$	$\frac{5}{16}$	$\frac{1}{32}$	$6\frac{15}{32}$.20	4114	BLK4114	6	$\frac{7}{16}$
$\frac{1}{2}$	$\frac{29}{32}$	$\frac{3}{8}$	$\frac{3}{8}$	$6\frac{25}{32}$.28	4116	BLK4116	6	$\frac{1}{2}$
$\frac{9}{16}$	$1\frac{1}{32}$	$\frac{7}{16}$	$\frac{7}{16}$	$6\frac{25}{32}$.30	4118	BLK4118	6	$\frac{9}{16}$
$\frac{5}{8}$	$1\frac{1}{16}$	$\frac{1}{2}$	$\frac{1}{2}$	$7\frac{1}{8}$.38	4120	BLK4120	6	$\frac{5}{8}$
$\frac{11}{16}$	$1\frac{1}{8}$	$\frac{1}{2}$	$\frac{9}{16}$	$7\frac{3}{16}$.45	4122	BLK4122	6	$\frac{11}{16}$
$\frac{3}{4}$	$1\frac{1}{32}$	$\frac{9}{16}$	$\frac{5}{8}$	$7\frac{1}{16}$.53	4124	BLK4124	6	$\frac{3}{4}$
$\frac{13}{16}$	$1\frac{1}{32}$	$\frac{5}{8}$	$2\frac{1}{32}$	$7\frac{1}{2}$.60	4126	BLK4126	6	$\frac{13}{16}$
$\frac{7}{8}$	$1\frac{3}{8}$	$\frac{5}{8}$	$\frac{1}{16}$	$7\frac{1}{2}$.60	4128	BLK4128	6	$\frac{7}{8}$
$\frac{15}{16}$	$1\frac{7}{16}$	$\frac{5}{8}$	$\frac{3}{4}$	$7\frac{13}{16}$.63	4130	BLK4130	6	$\frac{15}{16}$
1	$1\frac{9}{16}$	$1\frac{1}{16}$	$\frac{3}{4}$	$7\frac{13}{16}$.69	4132	BLK4132	6	1
$1\frac{1}{16}$	$1\frac{3}{8}$	$\frac{3}{4}$	$\frac{13}{16}$	$7\frac{15}{16}$.78	4134	BLK4134	6	$1\frac{1}{16}$
$1\frac{1}{8}$	$1\frac{11}{16}$	$\frac{25}{32}$	$\frac{7}{8}$	$7\frac{15}{16}$.83	4136	BLK4136	6	$1\frac{1}{8}$
$1\frac{1}{4}$	$1\frac{23}{32}$	$\frac{13}{16}$	1	$7\frac{15}{16}$.83	4140	BLK4140	6	$1\frac{1}{4}$
$1\frac{3}{8}$	$2\frac{3}{32}$	$\frac{29}{32}$	$1\frac{1}{16}$	9	1.3	4144	BLK4144	6	$1\frac{3}{8}$
$1\frac{1}{2}$	$2\frac{1}{16}$	$\frac{7}{8}$	1	10	1.6	4148	BLK4148	6	$1\frac{1}{2}$