


Double Offset Box Wrenches



American Alloy Steel

Drop Forged

12 Point Box

Double Offset 45° for
Obstruction Clearance

Different Opening in Each End.

Short Pattern

Wrench Opening	Diameter of Head		Thickness of Head		Length	Wt. Ea. Lbs.	Chrome	Industrial Black	Std. Pkg. Qty.	Wrench Opening
	A ₁	B ₁	A ₂	B ₂			Part No.	Part No.		A × B
A × B	A ₁	B ₁	A ₂	B ₂	C					A × B
5/16 × 3/8	1/32	3/64	7/32	1/4	4 1/4	.06	9721	BLK9721	6	5/16 × 3/8
3/8 × 7/16	1/32	5/8	1/64	5/16	4 5/8	.08	9723	BLK9723	6	3/8 × 7/16
7/16 × 1/2	5/8	23/32	5/16	1/32	5 1/16	.10	9725	BLK9725	6	7/16 × 1/2
1/2 × 9/16	23/32	1/16	1/32	3/8	5 1/2	.13	9725B	BLK9725B	6	1/2 × 9/16
9/16 × 5/8	1/16	7/8	3/8	7/16	5 5/16	.19	9727	BLK9727	6	9/16 × 5/8
5/8 × 1/4	7/8	1 1/32	7/16	1/32	6 1/2	.26	9727A	BLK9727A	6	5/8 × 1/4
5/8 × 3/4	7/8	1 1/32	7/16	1/32	6 1/2	.25	9729	BLK9729	6	5/8 × 3/4

Long Pattern

Wrench Opening	Diameter of Head		Thickness of Head		Length	Wt. Ea. Lbs.	Chrome	Industrial Black	Std. Pkg. Qty.	Wrench Opening
	A ₁	B ₁	A ₂	B ₂			Part No.	Part No.		A × B
3/8 × 7/16	1/32	1/32	5/32	5/32	6 1/32	.15	8723	BLK8723	6	3/8 × 7/16
7/16 × 1/2	5/8	1/16	5/16	5/16	7 3/4	.16	8725	BLK8725	6	7/16 × 1/2
1/2 × 9/16	1 1/16	13/16	3/8	3/8	8 5/8	.25	8725B	BLK8725B	6	1/2 × 9/16
9/16 × 5/8	23/32	7/8	3/8	3/8	9 1/2	.34	8727	BLK8727	6	9/16 × 5/8
5/8 × 1/4	7/8	3/32	1/32	1/32	10 1/16	.37	8727A	BLK8727A	6	5/8 × 1/4
5/8 × 3/4	7/8	1 1/32	23/64	23/64	11 3/16	.43	8729	BLK8729	6	5/8 × 3/4
1/16 × 3/4	1 1/32	1 5/32	1 5/32	1 5/32	11 7/8	.56	8029B	BLK8029B	6	1/16 × 3/4
3/4 × 7/8	1 1/32	1 3/16	1/2	1/2	12 3/16	.68	8731A	BLK8731A	6	3/4 × 7/8
13/16 × 7/8	1 1/32	1 1/32	1 1/32	1 1/32	13 3/16	.74	8731B	BLK8731B	6	13/16 × 7/8
7/8 × 15/16	1 3/16	1 13/32	9/16	9/16	14 1/16	1.0	8033A	BLK8033A	6	7/8 × 15/16
1 1/16 × 1	1 3/16	1 13/32	9/16	9/16	14 1/16	1.0	8033C	BLK8033C	6	1 1/16 × 1
1 × 1 1/8	1 13/32	1 17/32	2 1/32	2 1/32	15 3/16	1.4	8735	BLK8735	6	1 × 1 1/8
1 1/16 × 1 1/8	1 13/32	1 17/32	2 1/32	2 1/32	15 3/16	1.4	8735A	BLK8735A	6	1 1/16 × 1 1/8
1 1/16 × 1 1/4	1 3/16	1 13/16	1 1/16	1 1/16	17 3/16	1.8	8037	BLK8037	1	1 1/16 × 1 1/4
1 1/8 × 1 1/16	1 3/16	1 13/16	1 1/16	1 1/16	17 3/16	1.8	8037A	BLK8037A	1	1 1/8 × 1 1/16
1 1/4 × 1 1/16	1 7/8	2 1/16	3/4	3/4	18 3/8	2.4	8039B	BLK8039B	1	1 1/4 × 1 1/16
1 1/4 × 1 7/16	1 7/8	2 1/16	3/4	3/4	18 3/8	2.4	8039	BLK8039	1	1 1/4 × 1 7/16
1 5/16 × 1 1/2	2	2 1/16	25/32	13/16	20 1/16	2.8	8040A	BLK8040A	1	1 5/16 × 1 1/2
1 3/8 × 1 7/16	2	2 1/16	25/32	13/16	20 1/16	2.8	8040C	BLK8040C	1	1 3/8 × 1 7/16
1 3/8 × 1 1/2	2	2 1/16	25/32	13/16	20 1/16	2.8	8040	BLK8040	1	1 3/8 × 1 1/2
1 1/16 × 1 1/2	2	2 1/16	25/32	13/16	20 1/16	2.8	8040B	BLK8040B	1	1 1/16 × 1 1/2